


Product Name :
Torsional Vibrational Apparatus

Product Code :
CHINAELABC2580025



Description :

Torsional Vibrational Apparatus

Technical Specification :

This bench top mounted unit is used to study torsion and torsional vibration in experiments.

The apparatus is constructed around a profilled aluminium base with leveling feet, onto which is mounted 4 vertical chuck pillars.

Each pillar contains a central shaft running in precision bearings with a chuck at one end which grips a torsion specimen.

Each chuck also contains a large disc of varying mass and inertia.

With these chucks it is possible to assemble a torsion specimen with up to 3 masses.

Vibrations are transmitted into the torsion specimen by means of an exciter, which is electronically speed controlled from the main control unit.

To change the end conditions of the apparatus a fifth chuck houses a chuck which rigidly clamps the end of the torsion specimen to achieve a fixed end.

Also supplied with the apparatus is a manual torsion arrangement, which allows a known angular twist to be applied to the specimen.

A cord is wrapped around one of the large discs and a load is applied via a hanger and weights set.

The angle of twist for incremental loading is recorded and the modulus of rigidity can be calculated.

Oscillations sensors are mounted integrally with each mass pillar and provide signals of the amplitude of vibration.

The control unit conditions these signals and makes them available to an oscilloscope (not supplied) for vibration analysis.

Unit for investigating torsional vibration and torsional stiffness.

Observation of resonance, phase change.

To be made from profiled aluminum with levelling feet at each corner.

To have steel torsion bar, corrosion-resistant, 1300mm long, $\varnothing 6$ mm with torsional mass discs of $\varnothing 150$ mm and $\varnothing 228$ mm.

To have speed-controlled exciter with drive crank.

Angular movement of shaft recorded using oscillation sensors.

Electronic exciter control unit with digital display.

Torsion arrangement for modulus of rigidity experiments.

4 movable chuck pillars with integral bearings, the bearing units can be positioned as required.



Engineering Lab China